

BriskHeat[®]
Corporation

NEW

Ideal for:

**Laboratory
Heating
and
Oil Bath
Applications**

Beaker Heaters


- Easy-to-Install and Remove
- Moisture and Chemical Resistant
- Uniform Heat Across Surface of Beaker



W
W
W
BriskHeat.
C
O
M

Specifications:

- Fits Griffin and standard size beakers
- Maximum exposure temperature: 232°C (450°F)
- Hook and loop closure (like VELCRO[®]), allows for quick installation and removal
- Easily view graduation during set-up and operation
- Moisture and chemical resistant
- Heating element is laminated between two layers of 15mil fiberglass reinforced silicone rubber
- Power density: 5.0 watts/in² (0.008 watts/mm²)
- Dielectric strength of over 2000 volts
- 120 or 240VAC
- 2-ft (61 cm) long power leads with
 - 120VAC: Standard 2-prong plug (NEMA 1-15)
 - 240VAC: Bare wire connection
- Requires a temperature or power controller
- **CE** 73/23/EC (Low Voltage Directive)



Ordering Information

Size ml	Diameter in (mm)	Heater Height in (mm)	Heater Width in (mm)	Total Watts	Part Number 120VAC	Part Number 240VAC
250	2.7 (69)	3.0 (76)	12.25 (311)	150	GBH0250-1	GBH0250-2
400	3.0 (76)	3.5 (89)	13.75 (349)	200	GBH0400-1	GBH0400-2
600	3.6 (91)	4.0 (102)	15.00 (381)	250	GBH0600-1	GBH0600-2
1000	4.3 (109)	4.6 (117)	17.25 (438)	350	GBH1000-1	GBH1000-2

Need a different size or have a different object to heat?

We can design a heater specifically for your application. Contact us or your local distributor for a quote.

BriskHeat offers a complete line of heating and control solutions



Temperature Controls



Mantle Heaters

XtremeFLEX[®]



Flexible Heating Tapes



Cloth Jackets and Insulators

Your **Heating Specialist** since 1949